

40.32.25 - Motoc. BlueStar Med. 404

(related parameters)	(compressor type)	MQ-GQR70K		(test number)	2019-4-3-1		
	(prototype number)	03304#		(test basis)	GB/T9098-2008	(testing speed)	2
	(producing area)			(type of compressor)		(speed)	
	(capacitance)			(Cryogen)	R404a	(rated capacity)	
	(rated capacity)			(rated power)		(rated COP)	
test condition	(project)	(evaporation temperature)	(condensing temperature)	(suction temperature)	supercooling temperature	(ambient temperature)	
	(parameters)	-23,3	54,4	32,2	32,2	32,2	
(project)	unit	(Record one)	(Record two)	(Record three)	(Record	(average)	
(supply voltage)	V	219,8	219,8	219,8	219,8	219,8	
(supply current)	A	2,11	2,11	2,11	2,11	2,11	
(supply frequency)	Hz	50	50	50	50	50	
(input power)	W	292,35	291,91	291,87	291,9	292,01	
(power factor)	/	0,63	0,63	0,63	0,63	0,63	
(evaporation temperature)	°C	-23,33	-23,38	-23,37	-23,37	-23,36	
(condensation temperature)	°C	54,44	54,4	54,42	54,41	54,42	
(supercooling temperature)	°C	32,18	32,19	32,21	32,21	32,2	
(suction temperature)	°C	32,25	32,19	32,19	32,18	32,2	
(ambient temperature)	°C	32,2	32,17	32,25	32,26	32,22	
(exhaust temperature)	°C	82,91	82,73	82,71	82,7	82,76	
(condenser outlet Temp)	°C	35,33	35,06	34,91	34,85	35,04	
(calorimeter outlet Temp)	°C	31,99	31,94	31,92	31,92	31,94	
(shell temperature)	°C	65,08	65	64,99	64,89	64,99	
(vessel room temperature)	°C	26,56	26,52	26,44	26,49	26,5	
(suction pressure)	MPa	0,2737	0,2731	0,2732	0,2733	0,2733	
(exhaust pressure)	MPa	2,5548	2,5528	2,5537	2,5535	2,5537	
calorimeter-inlet Press)	MPa	2,5621	2,56	2,561	2,5608	2,561	
(pressure in the calorimeter)	MPa	0,4243	0,4243	0,4242	0,4244	0,4243	
(calorimeter-Outlet Press)	MPa	0,2737	0,2731	0,2731	0,2732	0,2733	
(calorimeter heating power)	W	378,2	378,37	378,5	378,87	378,49	
(cooling capacity)	W	378,58	379,49	379,69	379,98	379,44	
COP	/	1,295	1,3	1,301	1,302	1,3	
(compressor speed)	r/min	0	0	0	0	0	
(cold-main winding)	Ω	7,47		(cold- secondary winding)	16,95		
(cold-state temperature)	°C	20,34		(winding			
(hot-main winding)	Ω	8,73		(hot- secondary winding)	21,86		
(main winding resistance temperature)	°C	61,92		(secondary winding resistance temperature)	91,46		

www.ansal.com.ar

Toda la información contenida en este instructivo está sujeta a cambios sin previo aviso.

